

LTPA 64/128 - 10Gb

Built on the latest MicroPulse LTPA developments, the LTPA 64/128 – 10Gb provides all the high performance and flexibility of the existing LTPA 64/128 ultrasonic inspection system, but introduces a 10Gb ethernet interface for users that wish to really maximise the speed of their data transfer and truly accelerate the capability for your advanced acquisition processes such as FMC. All LTPA's are completely enclosed units, capable of conventional, phased array and FMC, VSA and PWI acquisition processes.



Overview

The LTPA 64/128 - 10Gb is a high speed data transfer version of the standard LTPA instrument. With a 10Gb Ethernet interface the instrument seriously speeds up your inspections where data transfer rates are a limitation, such as FMC.

It connects to the PC running the test application via the 10Gb Ethernet and takes its power over ethernet or from a separate 48 V power source.

With all the high performance and low noise ultrasonic characteristics delivered by the standard LTPA, the instrument retains the compact (120mm x 280mm x 310mm), rugged, lightweight (< 5Kg) and enclosed unit (no fans).

Additionally the 10Gb unit has 4 conventional channels (pulse echo or pitch-catch) available.

Software Platforms

The long-established open and transparent data format MicroPulse command language allows direct access to the instrument control allowing users to develop their own custom applications to meet their specific needs.

Supplied in the box, Peak NDT's ArrayGen software will get you started, then the choices are yours. Off-the-shelf solutions are available such as Utex Scientifics Inspectionware and TWI's Crystal FMC platform both of which have been long developed with the MicroPulse range of instruments.

If a bespoke application is what's required then using Peak NDT's focal law calculation.dll with the transparent data formats and standard sockets make writing custom applications a breeze. Customers have developed applications in a range of languages such as C, C+, Matlab and Labview as a few examples.

Features

- Very High data output 10Gb Ethernet link
- 4 conventional channels available for pulse-echo or pitch-catch
- Small/rugged/lightweight
- Power over Ethernet (PoE)
- No external fans unique air cradle maintains internal temperature
- All channels available for beam forming
- High power phased array channels user definable pulser voltage available up to 200V
- Inputs for 2 axes of encoders (single-ended or differential) for true pulse on position
- Outputs digitised waveform and/or peakdetected data with up to 4 hardware gates

Applications

- Pipeline girth weld inspection
- Inline testing systems
- Research and Development

Full Information available at www.peakndt.com

LTPA 10Gb PA Channels

	Parameter	Range	Step Size
Configurations		64/128 - one Hypertronics (1-128)	
Pulser	Pulser Type	Negative square wave	-
	Pulser Voltage	50 to 200Volts	25Volt
	Pulser Rise Time	<5ns	-
	Pulser Width	20nsec to 500nsec	2nsec
	Pulser Output Impedance	<10Ω	-
	Pulser Damping	100Ω	-
	Pulse Repetition Frequency	1Hz to 20kHz	1Hz
	Parallel Firing	No	
	Phased Array Pulser Delay	0 to 25000nsec	1nsec
	Number of Tx Focal Laws Tx Voltage Apodistion	Up to 2048 No	-
Receiver	Oate	70.40	0.05 ID
	Gain	70dB	0.25dB
	Coin Lincarity	NB Max DAC plus main gain is 110dB	
	Gain Linearity	Better than 0.25dB	-
	Input Impedance Bandwidth	100Ω	-
	Analogue Filters	0.75MHz to 20MHz (-3dB) 0.75MHz to 5MHz (-3dB) Bandpass	discrete selection
	Analogue Filters	5MHz to 10MHz (-3dB) Bandpass	discrete selection
		2MHz to 10MHz (-3dB) Bandpass	
	Digital Filters	Programmable high and low pass	User definable
	Phased Array Receiver Delay	0 to 25000nsec	1nsec
	Number of Rx Focal Laws	Up to 2048	-
	Dynamic Depth Focusing	At 100MHz realtime	_
	Channel Crosstalk	>60dB between channels at 2MHz	-
Distance	DAC Dynamic Range	0 to 60dB	0.25dB
Amplitude	DAC Trigger	Transmit pulse or material interface echo	Selectable
Correction	No of DAC curves	2048 utilising up to 64kbytes	-
	DAC update	40dB/µsec	-
	DAC Clock	0.78125MHz, 1.5625MHz, 3.125MHz, 6.25MHz,	6 settings (selectable
	Water path DAC	12.5MHz and 25MHz selectable	
Digitiser	ADC Resolution	12 bits	N/A
and Digital	Amplitude Resolution	16 bits	1077
Processing	Sample Rate	10, 25, 50 and 100MHz	Selectable
	Number of ADC's	One per two channels	
	Element Summing	Up to 512 channels	N/A
	Acquisition Gate Delay	64k sample points from trigger or I/F echo	1 sample point
	Acquisition Gate	Up 32K sample points	1 sample point
	Rectification	No Rectification	Selectable
		Fullwave	
		+ve halfwave	
		-ve halfwave	
	Smoothing	None and 10 selectable settings	N/A
	Hardware Gates	4 gates utilising up to 32K samples each	
	Interface Echo	Hardware interface trigger for gate and DAC	
	Hardware Peak Processing	For each gate up to 80 peaks (N + largest), first peak, largest peak, threshold crossing	
	Output Options	Peak processed data and/or full digitised	
	Threshold	waveform	1
	Averaging	10 to 4095	
	Gain Reduced Firing	2 to 256 realtime	
		1 element, n elements or summed waveform	

LTPA 10Gb Conventional Channels

	Parameter	Range	Step Size
Configurations		4 p/e or TOFD	
Pulser	Pulser Type	Negative square wave	-
	Pulser Voltage	25 to 200Volts	25Volt
	Pulser Rise Time	<5ns	-
	Pulser Width Pulser Output Impedance	16nsec to 1010nsec <10Ω	2nsec
	Pulser Damping	50Ω too 660Ω in 8 steps	-
	Pulse Repetition Frequency	1Hz to 20kHz	1Hz
	Parallel Firing	No	
Receiver	Gain	70dB	0.25dB
		NB Max DAC plus main gain is 110dB	
	Gain Linearity	Better than 0.25dB	-
	Input Impedance	660Ω	-
	Bandwidth Analogue Filters	0.75MHz to 25MHz (-3dB) 0.75MHz to 12MHz (-3dB) Bandpass	discrete selection
	Analogue Filters	2.5MHz to 18MHz (-3dB) Bandpass	discrete selection
		3MHz to 22MHz (-3dB) Bandpass	
		3MHz to 25MHz (-3dB) Bandpass	
		0.5MHz Bandpass Filter	
		1MHz Bandpass Filter 2MHz Bandpass Filter	
		4MHz Bandpass Filter	
		5MHz Bandpass Filter	
		10MHz Bandpass Filter	
		5MHz 2nd order TOFD Bandpass Filter	
	District Files	10MHz 2nd order TOFD Bandpass Filter	l la anala finala la
	Digital Filters Channel Crosstalk	Programmable high and low pass >60dB between channels at 2MHz	User definable
	Chamiler Crosstaik	>00ub between channels at 2MH2	
Distance	DAC Dynamic Range	0 to 60dB	0.25dB
Amplitude Correction	DAC Trigger	NB Max DAC plus main gain is 110dB Transmit pulse or material interface echo	Selectable
Correction	No of DAC curves	256 utilising up to 64kbytes	-
	DAC update	40dB/µsec	-
	DAC Clock	0.78125MHz, 1.5625MHz, 3.125MHz, 6.25MHz,	6 settings (selectable
		12.5MHz and 25MHz selectable	
	Water path DAC		
Digitiser and Digital	ADC Resolution Amplitude Resolution	12 bits 16 bits	-
Processing	Sample Rate	10, 25, 50 and 100MHz	Selectable
	Number of ADC's	1 per channel	
	Element Summing	N/A	N/A
	Acquisition Gate Delay	64k sample points from trigger or I/F echo	1 sample point
	Acquisition Gate Rectification	Up 32K sample points No Rectification	1 sample point Selectable
	Recuircation	Fullwave	Selectable
		+ve halfwave	
		-ve halfwave	
	Smoothing	None and 10 selectable settings	-
	Hardware Gates	4 gates utilising up to 32K samples each	-
	Interface Echo Hardware Peak Processing	Hardware interface trigger for gate and DAC For each gate up to 80 peaks (N + largest), first peak,	- Selectable
		largest peak, threshold crossing	Selectable
	Output Options	Peak processed data and/or full digitised waveform	1
	Threshold Averaging	10 to 4095 2 to 256 realtime	1
		7 10 7 30 TEALITHE	
	Gain Reduced Firing	Selectable to be triggered on saturation with	

General Specification

Interfaces Communication Interface

10 Gigabit Ethernet **Output Data Buffer** 4Gbytes

FMC Acquisition Buffer

Uses output buffer Digital Encoders 2 axes of differential 32-bit encoder inputs accepting 5Volt encoders

at rate of up to 700kHz

4 inputs and 4 outputs (5Volt TTL compatible) Digital I/O

Analogue Outputs Trigger

Connectors UT Connectors PA

160-pin female connector. Hypertronics™ HLMYJPAPF 1600 **UT Connectors Conventional** Coaxial Lemo 00 Industrial RJ45 **Ethernet Connector**

Encoder Connector Lemo 1B.310 I/O Connector Lemo 0B.306 **Power Connector** Lemo 0B.302 Analogue O/P Connectors Lemo 1B.310

Physical Case Size (H x W X D)

120mm x 280mm x 310mm Power Supply 48V DC separate supply (48V @ 1250mA)

Power Consumption 60W max

Weight Up to 5 Kgs depending on configuration

Environmental Operating / Storage Conditions Operating Temperature: 0 to 45°C

Storage Temperature: -10 to 55°C

Relative Humidity: less than 85% non-condensing

ЕМС EN61326 EN61010 Safety